

Eaton HJDB3200

Catalog Number: HJDB3200

Series C, J-frame molded case circuit breaker, 200A, Three-pole, Interchangeable thermal magnetic trip, HJDB breaker



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HJDB3200
	UPC
	782113928845
Product Length/Depth	Product Height
4.06 in	4.13 in
Product Width	Product Weight
4.13 in	12.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Product specifications

Interrupt rating

100 kAIC at 240 Vac

25 kAIC at 600 Vac

65 kAIC at 480 Vac

Type

Complete breaker

Frame

J

Circuit breaker type

HJDB

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Voltage rating

600 Vac, 250 Vdc

Amperage Rating

200 A

Trip Type

Interchangeable thermal-magnetic

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Eaton Specification Sheet - HJDB3200](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)