

Eaton HJDDC3125W

Catalog Number: HJDDC3125W

Eaton Series C DC/PvGard complete molded case circuit breaker, J-frame, HJD, Complete breaker, Interchangeable thermal-magnetic trip type, Three-pole, 125A, 600 Vdc, 42 kAIC at 600 Vdc, Without terminals, Vdc



General specifications

Product Name	Catalog Number
Eaton PV Guard / Solar complete molded case circuit breaker	HJDDC3125W
	UPC
	786679072271
Product Length/Depth	Product Height
4.06 in	4.13 in
Product Width	Product Weight
4.13 in	12.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL 489 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Product specifications

Interrupt rating

42 kAIC at 600 Vdc

Type

Complete breaker

Frame

J

Circuit breaker type

HJD

Class

Vdc

Circuit breaker frame type

Complete breaker

Terminals

Without terminals

Voltage rating

600 Vdc

Amperage Rating

125 A

Trip Type

Interchangeable thermal-magnetic

Number of poles

Three-pole

Resources

Brochures

[PVGard solar circuit breakers product aid](#)

[DC molded-case circuit breakers and switches](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Value of Circuit Breakers for PV Systems and Eaton PVGard Solar Circuit Breakers](#)

Specifications and datasheets

[PVGard solar circuit breakers technical data sheet](#)

[Eaton Specification Sheet - HJDDC3125W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)