

Eaton HKDDC3400WA02T26

Catalog Number: HKDDC3400WA02T26

Eaton Series C DC/PvGard complete molded case circuit breaker, K-frame, HKD, Interchangeable thermal-magnetic trip, Three-pole, 400A, 600 Vac, 250 Vdc, 42 kAIC at 600 Vac, No term., 1A-1B rear w/left pigtail, 24 Vdc rear w/ right pigtail



General specifications

Product Name

Eaton PV Guard / Solar complete
molded case circuit breaker

Catalog Number

HKDDC3400WA02T26

UPC

786679116548

Product Length/Depth

4.1 in

Product Height

5.5 in

Product Width

5.5 in

Product Weight

12.9 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL 489
from the date of installation of the
Product or eighteen (18) months from the
date of shipment of the Product,
whichever occurs first.

Certifications

Product specifications

Interrupt rating

42 kAIC at 600 Vac

Frame

K

Amperage Rating

400 A

Number of poles

Three-pole

Circuit breaker type

HKD

Shunt trip

12-24 Vac/dc rear with left pigtail shunt

Undervoltage release

24 Vdc rear with right pigtail

Class

Vdc

Circuit breaker frame type

Complete breaker

Terminals

Without terminals

Voltage rating

600 Vac, 250 Vdc

Auxiliary switch

1A-1B rear with left pigtail

Trip Type

Interchangeable thermal-magnetic

Resources

Brochures

[PVGard solar circuit breakers product aid](#)

[DC molded-case circuit breakers and switches](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Value of Circuit Breakers for PV Systems and Eaton PVGard Solar Circuit Breakers](#)

Specifications and datasheets

[PVGard solar circuit breakers technical data sheet](#)

[Eaton Specification Sheet - HKDDC3400WA02T26](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)