

Eaton HLDDC21200

Catalog Number: HLDDC21200

Eaton Series C DC/PvGard complete molded case circuit breaker, L-frame, HLD, Complete breaker, Fixed thermal, fixed magnetic trip type, Two-pole, 1200A, 250 Vdc, 50 kAIC at 250 Vdc, Line and load, Vdc

General specifications



Product Name	Catalog Number
Eaton PV Guard / Solar complete molded case circuit breaker	HLDDC21200
	UPC
	782113964454
Product Length/Depth	Product Height
4.06 in	8.25 in
Product Width	Product Weight
8.25 in	35 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL 489 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Product specifications

Interrupt rating

50 kAIC at 250 Vdc

Frame

L

Circuit breaker type

HLD

Class

Vdc

Terminals

Line and load

Voltage rating

250 Vdc

Amperage Rating

1200 A

Trip Type

Fixed thermal, fixed magnetic

Number of poles

Two-pole

Resources

Brochures

[PVGard solar circuit breakers product aid](#)

[DC molded-case circuit breakers and switches](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Value of Circuit Breakers for PV Systems and Eaton PVGard Solar Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - HLDDC21200](#)

[PVGard solar circuit breakers technical data sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)