

Eaton JDCB3225

Catalog Number: JDCB3225

Series C, J-frame molded case circuit breaker, 225A, Three-pole, Non-interchangeable thermal magnetic trip, JDCB breaker

General specifications



Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	JDCB3225

UPC
782113928920

Product Length/Depth
4.06 in

Product Height
4.13 in

Product Width
4.13 in

Product Weight
9 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Product specifications

Interrupt rating

100 kAIC

Type

Complete breaker

Frame

J

Circuit breaker type

JDCB

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Voltage rating

600 Vac

Amperage Rating

225 A

Trip Type

Non-interchangeable thermal-magnetic

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Multi-wire lugs product aid](#)

[StrandAble terminals product aid](#)

[Motor protection circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - JDCB3225](#)