

Eaton KDCB3400FT32W

Catalog Number: KDCB3400FT32W

Eaton Series C electronic molded case circuit breaker, K-frame, KDCB, Complete breaker, Digitrip 310 RMS, Electronic LSI trip, Three-pole, 400A, 600 Vac, 100 kAIC at 480 Vac, Without terminals, Reverse feed, 100% protected neutral pole



General specifications

Product Name	Catalog Number
Eaton Series C electronic molded case circuit breaker	KDCB3400FT32W
	UPC
	782113714608
Product Length/Depth	Product Height
4.1 in	5.5 in
Product Width	Product Weight
5.5 in	11 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Product specifications

Interrupt rating

100 kAIC at 480 Vac

Type

Reverse feed

Frame

K

Circuit breaker type

KDCB

Functions

Reverse

Circuit breaker frame type

Complete breaker

Terminals

Without terminals

Voltage rating

600 Vac

Amperage Rating

400 A

Protection

100% protected neutral pole

Trip Type

Electronic LSI

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[StrandAble terminals product aid](#)

[Circuit breaker motor operators product aid](#)

[Motor protection circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Installation instructions

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - KDCB3400FT32W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)