

Eaton KG3300S41

Catalog Number: KG3300S41

Eaton Series C complete molded case circuit breaker, K-frame, KG, Fixed thermal, fixed magnetic trip, 500-1000A trip rating, Three-pole, 300A, 600 Vac, Line and load, 12-24 Vac/dc same side w/ left pigtail



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	KG3300S41
	UPC
	782116018901
Product Length/Depth	Product Height
6.2 in	6.9 in
Product Width	Product Weight
12.3 in	10 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Std. C22.2 No. 5 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	IEC Rated UL Listed IEC 947-2 UL 489

Product specifications

Interrupt rating

18 kAIC at 240 Vac

14 kAIC at 480 Vac

Frame

K

Trip rating

500-1000 A

Functions

Reverse

Amperage Rating

300 A

Number of poles

Three-pole

Type

Complete breaker

Circuit breaker type

KG

Shunt trip

12-24 Vac/dc same side with left pigtail shunt

Frequency rating

60 Hz

Class

Engine generator

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Voltage rating

600 Vac

Trip Type

Fixed thermal, fixed magnetic

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[StrandAble terminals product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[Series C Engine Generator Circuit Breakers - Dimension Sheets](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - KG3300S41](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)