

Eaton KG3350

Catalog Number: KG3350

Eaton Series C complete EG molded case circuit breaker, K-frame, KG, Thermal-magnetic trip, 500-1000A, Three-pole, 350A, 600 Vac, 18 kAIC at 240 Vac, 14 kAIC at 480 Vac, Line/load, Engine generator, Reverse feed, 60 Hz



General specifications

Product Name	Catalog Number
Eaton complete engine generator molded case circuit breaker	KG3350
	UPC
	786679197127
Product Length/Depth	Product Height
12 in	6 in
Product Width	Product Weight
7 in	11.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year IEC 947-2 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Std. C22.2 No. 5 CSA Certified UL 489 IEC Rated

Product specifications

Interrupt rating

14 kAIC at 480 Vac

18 kAIC at 240 Vac

Frame

K

Generator rating

126 kVA/101 kW at 240 Vac, 253 kVA/202 kW at 480 Vac, 316 kVA/253 kW at 600 Vac

Trip rating

500-1000 A

Functions

Reverse

Amperage Rating

350 A

Number of poles

Three-pole

Circuit breaker type

KG

Shunt trip

12-24 Vac/dc same side with left pigtail shunt

Frequency rating

60 Hz

Class

Engine generator

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Voltage rating

600 Vac

Trip Type

Thermal-magnetic

Resources

Catalogs

[Engine generator circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[Series C Engine Generator Circuit Breakers - Dimension Sheets](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - KG3350](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)