

Eaton KG3350S46Z04

Catalog Number: KG3350S46Z04

Eaton Series C complete EG molded case circuit breaker, K-frame, KG, Thermal-magnetic trip, 500-1000A, Three-pole, 350A, 600 Vac, 18 kAIC at 240 Vac, 14 kAIC at 480 Vac, 12-24 Vac/dc rear w/ right pigtail, Reverse feed, 60 Hz, 3TA400K



General specifications

Product Name

Eaton complete engine generator
molded case circuit breaker

Catalog Number

KG3350S46Z04

UPC

782113491608

Product Length/Depth

12 in

Product Height

6 in

Product Width

7 in

Product Weight

13 lb

Warranty

Eaton Selling Policy 25-000, one (1) year MIL-DTL-17361 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

IEC Rated
CSA Certified
UL Listed
IEC 947-2
UL 489
CSA Std. C22.2 No. 5
UL Listed file E7819
QPL17361

Catalog Notes

Includes both line and load terminals

Product specifications

Interrupt rating

14 kAIC at 480 Vac

18 kAIC at 240 Vac

Frame

K

Generator rating

126 kVA/101 kW at 240 Vac, 253 kVA/202 kW at 480 Vac, 316 kVA/253 kW at 600 Vac

Trip rating

500-1000 A

Functions

Reverse

Amperage Rating

350 A

Number of poles

Three-pole

Line

3TA400K

Prod load

3TA400K

Type

Engine generator

Circuit breaker type

KG

Shunt trip

12-24 Vac/dc right pigtail same side

Frequency rating

60 Hz

Class

Engine generator

Circuit breaker frame type

Complete breaker

Terminals

Without terminals, optional line and load

Voltage rating

Resources

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Engine generator circuit breakers catalog](#)

Drawings

[Series C Engine Generator Circuit Breakers - Dimension Sheets](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - KG3350S46Z04](#)

White papers

[Implementation of arc flash mitigating solutions at industrial manufacturing facilities](#)

600 Vac

Trip Type

Thermal-magnetic



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)