

Eaton KG3350W

Catalog Number: KG3350W

Eaton Series C complete EG molded case circuit breaker, K-frame, KG, Thermal-magnetic trip, 500-1000A, Three-pole, 350A, 600 Vac, 18 kAIC at 240 Vac, 14 kAIC at 480 Vac, No term., Engine generator, Reverse feed, 60 Hz



General specifications

Product Name	Catalog Number
Eaton complete engine generator molded case circuit breaker	KG3350W UPC 786679269466
Product Length/Depth	Product Height
12.25 in	6.9 in
Product Width	Product Weight
6.75 in	10 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year IEC Rated from the date of installation of the Product or eighteen (18) months from the UL Listed date of shipment of the Product, whichever occurs first.	CSA Certified IEC 947-2 UL 489 CSA Std. C22.2 No. 5

Product specifications

Interrupt rating

14 kAIC at 480 Vac

18 kAIC at 240 Vac

Frame

K

Generator rating

126 kVA/101 kW at 240 Vac, 253 kVA/202 kW at 480 Vac, 316 kVA/253 kW at 600 Vac

Trip rating

500-1000 A

Functions

Reverse

Amperage Rating

350 A

Number of poles

Three-pole

Circuit breaker type

KG

Frequency rating

60 Hz

Class

Engine generator

Circuit breaker frame type

Complete breaker

Terminals

Without terminals

Voltage rating

600 Vac

Trip Type

Thermal-magnetic

Resources

Catalogs

[Engine generator circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[Series C Engine Generator Circuit Breakers - Dimension Sheets](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - KG3350W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)