

Eaton KW3400V2D14Y39

Catalog Number: KW3400V2D14Y39

Eaton Series C complete molded case circuit breaker, K-frame, KW, Complete breaker, Adjustable thermal, adjustable magnetic trip type, Three-pole, 400A, 600 Vac, 250 Vdc, 45 kAIC at 415 Vac, Line side end cap, Metric, World, 50°C

General specifications



Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	KW3400V2D14Y39
	UPC
	782116883950
Product Length/Depth	Product Height
4.1 in	5.5 in
Product Width	Product Weight
5.5 in	12.7 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year IEC Rated from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	TA300K line

Product specifications

Interrupt rating

45 kAIC at 415 Vac

Frame

K

Calibration

50°C

Amperage Rating

400 A

Number of poles

Three-pole

Mounting hardware

Metric

Type

Complete breaker

Circuit breaker type

KW

Class

World

Circuit breaker frame type

Complete breaker

Terminals

Line side end cap

Voltage rating

600 Vac, 250 Vdc

Trip Type

Adjustable thermal, adjustable magnetic

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[StrandAble terminals product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Installation instructions

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - KW3400V2D14Y39](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)