

Eaton KW3400WS44X38Y02

Catalog Number: KW3400WS44X38Y02

Eaton Series C complete molded case circuit breaker, K-frame, KW, adj. thermal, adj. magnetic trip, Three-pole, 400A, 600 Vac, 250 Vdc, 45 kAIC at 415 Vac, No term., optional line or load, World, 12-24 Vac/dc same side left term.

General specifications



Product Name

Eaton Series C complete molded case circuit breaker

Catalog Number

KW3400WS44X38Y02

UPC

782116904464

Product Length/Depth

4.1 in

Product Height

5.5 in

Product Width

5.5 in

Product Weight

13.7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year IEC Rated from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

3TA400K6K load, TA350K line

Product specifications

Interrupt rating

45 kAIC at 415 Vac

Type

Complete breaker

Frame

K

Circuit breaker type

KW

Shunt trip

208-380 Vac or 110-127 Vdc left pigtail rear

Class

World

Circuit breaker frame type

Complete breaker

Terminals

Without terminals, optional line or load

Voltage rating

600 Vac, 250 Vdc

Amperage Rating

400 A

Trip Type

Adjustable thermal, adjustable magnetic

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Current limiting Series C molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Installation instructions

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C J-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - KW3400WS44X38Y02](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C F-Frame molded case circuit breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)