

Eaton KW4400KW23

Catalog Number: KW4400KW23

Eaton Series C molded case switch, K-frame, KW, Molded case switch, Adjustable thermal, adjustable magnetic trip type, Four-pole, 400A, 600 Vac, 250 Vdc, 45 kAIC at 415 Vac, Without terminals, World, Walking beam provisions



General specifications

Product Name

Eaton Series C molded case switch

Catalog Number

KW4400KW23

UPC

782116333721

Product Length/Depth

4.1 in

Product Height

7.22 in

Product Width

7.22 in

Product Weight

15.7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

IEC Rated

Product specifications

Special features

Walking beam provisions

Interrupt rating

45 kAIC at 415 Vac

Frame

K

Amperage Rating

400 A

Interlock

Four-pole left-hand 400A provisions for walking beam interlock

Number of poles

Four-pole

Type

Complete breaker

Circuit breaker type

KW

Class

World

Circuit breaker frame type

Molded case switch

Terminals

Without terminals

Voltage rating

600 Vac, 250 Vdc

Trip Type

Adjustable thermal, adjustable magnetic

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Plug-in adapters for molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[StrandAble terminals product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Installation instructions

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - KW4400KW23](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)