

# Eaton LA3175PRW

Catalog Number: LA3175PRW

Eaton Classic complete molded case circuit breaker, LA, Interchangeable thermal-magnetic trip, 875-1750A trip rating, Three-pole, 175A, 600 Vac, 250 Vdc, 200 kAIC at 600 Vac, 100 kAIC at 250 Vdc, Copper, No terminals, Pressure, Pressure

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Classic complete molded case circuit breaker	LA3175PRW
	<b>UPC</b>
	782114342992
<b>Product Length/Depth</b>	<b>Product Height</b>
0.01 in	0.01 in
<b>Product Width</b>	<b>Product Weight</b>
0.01 in	0.01 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL 489 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Product specifications

### Interrupt rating

100 kAIC at 250 Vdc

200 kAIC at 600 Vac

### Trip rating

875-1750 A

### Amperage Rating

175 A

### Number of poles

Three-pole

### Line

Pressure

### Prod load

Pressure

### Type

Complete breaker

### Circuit breaker type

LA

### Circuit breaker frame type

Complete breaker

### Terminals

Without terminals

### Voltage rating

600 Vac, 250 Vdc

### Terminal material

Copper

### Trip Type

Interchangeable thermal-magnetic

### Magnetic trip range

875-1750A

## Resources

### Catalogs

[Miniature and Molded Case Circuit Breakers](#)

[Eaton Metering devices, protective relays, software and connectivity](#)

### Multimedia

[Circuit Breakers Explained](#)

### Specifications and datasheets

[Eaton Specification Sheet - LA3175PRW](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)