

Eaton XT IEC contactor

XTAS250L22A070

UPC:782116890408

Dimensions:

- **Height:** 12 IN
- **Length:** 8 IN
- **Width:** 6 IN

Weight:2.5 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 250A
- **Coil Voltage:** 110 Vac 50 Hz, 120 Vac, 60 Hz
- **Contact Configuration:** 2NO-2NC
- **Frame Size:** 140 mm
- **Frequency Rating:** 50-60 Hz
- **Operation:** Non-reversing
- **Overload Range:** 50-70A
- **Series:** XT IEC series|S-series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing starter

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTAS250L22A070](#)

Certifications:

- EN 60947
- CSA Certified
- IEC 60947
- UL Listed

Product compliance:

- CE Marked
- RoHS Compliant

- ATEX Compliant

© 2016 Eaton. All rights reserved.