

# Eaton XT IEC contactor

**XTAS250L22B220**

**UPC:**782116890507

## **Dimensions:**

- **Height:** 12 IN
- **Length:** 8 IN
- **Width:** 6 IN

**Weight:**2.5 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

## **Warranties:**

- 1 year

## **Specifications:**

- **Amperage Rating:** 250A
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 2NO-2NC
- **Frame Size:** 140 mm
- **Frequency Rating:** 50-60 Hz
- **Operation:** Non-reversing
- **Overload Range:** 160-220A
- **Series:** XT IEC series|S-series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing starter

## **Supporting documents:**

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTAS250L22B220](#)

## **Certifications:**

- IEC 60947
- EN 60947
- UL Listed
- CSA Certified

## **Product compliance:**

- ATEX Compliant
- RoHS Compliant

- CE Marked

---

© 2016 Eaton. All rights reserved.