

## Eaton XT IEC contactor

**XTCE012B10C-QC1**

**UPC:**786685284996

### Dimensions:

- **Height:** 1 IN
- **Length:** 1 IN
- **Width:** 1 IN

**Weight:**1 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 12A
- **Coil:** 412V 50 Hz, 480V 60 Hz
- **Coil Voltage:** 412 Vac 50 Hz, 480 Vac 60 Hz
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 1, 2, 2/ 3, 3, 10, 10 hp (1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eaton Specification Sheet - XTCE012B10C-QC1](#)

### Certifications:

- IEC 60947
- CSA Certified
- EN 60947
- UL Listed



**Product compliance:**

- RoHS Compliant
- CE Marked

---

© 2016 Eaton. All rights reserved.