

## Eaton XT IEC contactor

XTCE025C10B-QC1

UPC:786685285030

### Dimensions:

- Height: 1 IN
- Length: 1 IN
- Width: 1 IN

Weight:1 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 25A
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 2, 3, 5/ 7.5, 10, 15, 20 hp  
(1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eaton Specification Sheet - XTCE025C10B-QC1](#)

### Certifications:

- EN 60947
- UL Listed
- CSA Certified
- IEC 60947

### Product compliance:



- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.