

Eaton XT IEC contactor

XTCE050DS1B

UPC:786685457833

Dimensions:

- **Height:** 1 IN
- **Length:** 1 IN
- **Width:** 1 IN

Weight:1 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 50A
- **Auxiliary Contact:** Side-mounted
- **Coil:** 220V 50 Hz, 240V 60 Hz
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 3, 7.5, 10/ 15, 20, 40, 50 hp
(1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_D 3D Inventor](#)
- [XTCE_D 2D Drawing Xchange](#)
- [XTCE_D 2D PDF](#)
- [XTCE_D 3D Model Xchange](#)
- [XTCE_D AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCE050DS1B](#)



Certifications:

- EN 60947
- IEC 60947
- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.