

Eaton XT IEC contactor

XTCE080F00A-LR

UPC:786685119595

Dimensions:

- **Height:** 7.25 IN
- **Length:** 4 IN
- **Width:** 5.22 IN

Weight:7 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Accessories:** TRANE only
- **Amperage Rating:** 80A
- **Coil:** 12V 50/60 Hz
- **Coil Voltage:** 12 Vac, 50-60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 7.5, 15, 15/ 25, 30, 60, 75 hp
(1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eaton Specification Sheet - XTCE080F00A-LR](#)

Certifications:

- CSA Certified
- IEC 60947
- EN 60947
- UL Listed



Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.