

## Eaton XT IEC contactor

XTCE080FS1C

UPC:786685457918

### Dimensions:

- **Height:** 1 IN
- **Length:** 1 IN
- **Width:** 1 IN

**Weight:**1 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 80A
- **Auxiliary Contact:** Side-mounted
- **Coil:** 412V 50 Hz, 480V 60 Hz
- **Coil Voltage:** 415 Vac 50 Hz, 480 Vac, 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 7.5, 15, 15/ 25, 30, 60, 75 hp  
(1/3PH @ 115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_F AutoCAD 2D Footprint](#)
- [XTCE\\_F 3D Inventor](#)
- [XTCE\\_F 3D Model Xchange](#)
- [XTCE\\_F 2D PDF](#)
- [XTCE\\_F 2D Drawing Xchange](#)
- [Eaton Specification Sheet - XTCE080FS1C](#)



**Certifications:**

- EN 60947
- IEC 60947
- CSA Certified
- UL Listed

**Product compliance:**

- RoHS Compliant
- CE Marked

---

© 2016 Eaton. All rights reserved.