

## Eaton XT IEC contactor

XTCE095FS1T

UPC:786685446714

### Dimensions:

- **Height:** 6.69 IN
- **Length:** 5.59 IN
- **Width:** 3.54 IN

**Weight:**2 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 95A
- **Coil Voltage:** 24 Vac, 50-60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame:** Frame F
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 40, 50, 100, 125 hp (3PH @200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCE\\_F 2D Drawing Xchange](#)
- [XTCE\\_F AutoCAD 2D Footprint](#)
- [XTCE\\_F 2D PDF](#)
- [XTCE\\_F 3D Inventor](#)
- [XTCE\\_F 3D Model Xchange](#)
- [Eaton Specification Sheet - XTCE095FS1T](#)



**Certifications:**

- UL Listed
- IEC Rated
- CSA Certified
- EN 60947
- IEC 60947

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.