

## Eaton XT IEC contactor

**XTCE115GS1C**

**UPC:**786685440330

### Dimensions:

- **Height:** 6.5 IN
- **Length:** 6.5 IN
- **Width:** 8.5 IN

**Weight:**5.48 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 115A
- **Auxiliary Contact:** Side-mounted
- **Coil:** 412V 50 Hz, 480V 60 Hz
- **Coil Voltage:** 480V 50 Hz, 500V 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 10, 25, 25/ 40, 50, 100, 100 hp  
(1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE\\_G 3D Inventor](#)
- [XTCE\\_G AutoCAD 2D Footprint](#)
- [XTCE\\_G 2D Drawing Xchange](#)
- [XTCE\\_G 2D PDF](#)
- [XTCE\\_G 3D Model Xchange](#)
- [Eaton Specification Sheet - XTCE115GS1C](#)



**Certifications:**

- IEC 60947
- CSA Certified
- EN 60947
- UL Listed

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.