

Eaton XT IEC contactor

XTCE170G00AD

UPC:786685213675

Dimensions:

- **Height:** 6.89 IN
- **Length:** 3.583 IN
- **Width:** 6.732 IN

Weight:4.8 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 170A
- **Coil:** 120 Vdc
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Max Hp Rating:** 10, 25, 30/ 40, 60, 125, 125 hp
(1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCE_G AutoCAD 2D Footprint](#)
- [XTCE_G 2D PDF](#)
- [XTCE_G 3D Model Xchange](#)
- [XTCE_G 2D Drawing Xchange](#)
- [XTCE_G 3D Inventor](#)
- [Eaton Specification Sheet - XTCE170G00AD](#)

Certifications:

- CSA Certified



- IEC 60947
- EN 60947
- UL Listed

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.