

Eaton XT IEC contactor

XTCE225H22WD

Dimensions:

- **Height:** 10 IN
- **Length:** 10.25 IN
- **Width:** 7.5 IN

Weight:8.85 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 225A
- **Coil Voltage:** 48-60 Vdc
- **Contact Configuration:** 2NO-2NC
- **Frame Size:** 140 mm
- **Max Hp Rating:** 50, 75, 150, 200 hp (3PH @200,240,480,600 V)
- **Number Of Poles:** Three-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Global Data Sheet - XTCE225H22WD](#)
- [Eaton Specification Sheet - XTCE225H22WD](#)

Certifications:

- UL Listed
- CSA Certified
- EN 60947
- IEC 60947

Product compliance: No Data



