

Eaton XT IEC contactor

XTCF020B00F

Dimensions:

- **Height:** 3.071 IN
- **Length:** 1.811 IN
- **Width:** 2.756 IN

Weight: .48501698 LB

Warranties: No Data

Specifications:

- **Amperage Rating:** 20A
- **Coil Voltage:** 230 Vac 50 Hz
- **Contact Configuration:** 0NO-0NC
- **Frequency Rating:** 50 Hz
- **Max Hp Rating:** 1, 2/3, 3, 10, 10 hp (1/3PH @ 115,230/200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCF_B AutoCAD 2D Footprint \(mm\)](#)
- [XTCF_B 2D PDF](#)
- [XTCF_B 3D Inventor](#)
- [XTCF_B 3D Model Xchange](#)
- [XTCF_B AutoCAD 2D Footprint](#)
- [XTCF_B 2D Drawing Xchange](#)
- [Global Data Sheet - XTCF020B00F](#)
- [Eaton Specification Sheet - XTCF020B00F](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



