

Eaton XT IEC contactor

XTCF020B00TD

Dimensions:

- **Height:** 2 IN
- **Length:** 3 IN
- **Width:** 3 IN

Weight: .61729433 LB

Notes: Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Warranties: No Data

Specifications:

- **Amperage Rating:** 20A
- **Coil Voltage:** 24 Vdc
- **Contact Configuration:** 0NO-0NC
- **Max Hp Rating:** 1, 2/3, 3, 10, 10 hp (1/3PH @115,230/200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF_B 2D PDF](#)
- [XTCF_B 2D Drawing Xchange](#)
- [XTCF_B AutoCAD 2D Footprint](#)
- [XTCF_B AutoCAD 2D Footprint \(mm\)](#)
- [XTCF_B 3D Inventor](#)
- [XTCF_B 3D Model Xchange](#)
- [Global Data Sheet - XTCF020B00TD](#)
- [Eaton Specification Sheet - XTCF020B00TD](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947



- EN 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.