

# Eaton XT IEC contactor

**XTCF032C10TD**

## Dimensions:

- **Height:** 3.34645669 IN
- **Length:** 5.43307087 IN
- **Width:** 2.28346457 IN

**Weight:** .61729433 LB

**Notes:** Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

**Warranties:** No Data

## Specifications:

- **Amperage Rating:** 32A
- **Coil Voltage:** 24-27 Vdc
- **Contact Configuration:** 1NO
- **Frame Size:** 45 mm
- **Max Hp Rating:** 7.5, 7.5, 10, 15 hp (3PH @200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

## Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF\\_C 2D PDF](#)
- [XTCF\\_C 2D Drawing Xchange](#)
- [XTCF\\_C 3D Model Xchange](#)
- [XTCF\\_C AutoCAD 2D Footprint \(mm\)](#)
- [XTCF\\_C 3D Inventor](#)
- [XTCF\\_C AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCF032C10TD](#)
- [Global Data Sheet - XTCF032C10TD](#)

## Certifications:

- UL Listed
- CSA Certified



- IEC 60947
- EN 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.