

# Eaton XT IEC contactor

**XTCF045C10AD**

**UPC:**786685217208

## Dimensions:

- **Height:** 2.75 IN
- **Length:** 4.5 IN
- **Width:** 4 IN

**Weight:**1.18 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

## Warranties:

- 1 year

## Specifications:

- **Amperage Rating:** 45A
- **Coil:** 120 Vdc
- **Contact Configuration:** 1NO
- **Continuous Ampere Rating:** 1000A
- **Frame Size:** 45 mm
- **Max Hp Rating:** 7.5, 10, 15, 20 hp (3PH  
@200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

## Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF\\_C 2D PDF](#)
- [XTCF\\_C 2D Drawing Xchange](#)
- [XTCF\\_C 3D Model Xchange](#)
- [XTCF\\_C 3D Inventor](#)
- [XTCF\\_C AutoCAD 2D Footprint](#)
- [XTCF\\_C AutoCAD 2D Footprint \(mm\)](#)
- [Eaton Specification Sheet - XTCF045C10AD](#)



**Certifications:**

- UL Listed
- IEC 60947
- CSA Certified
- EN 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.