

Eaton XT IEC contactor

XTCF045C10L

UPC:786685217277

Dimensions:

- **Height:** 2.75 IN
- **Length:** 4.5 IN
- **Width:** 4 IN

Weight:1.18 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 45A
- **Coil:** 380V 50 Hz, 440V 60 Hz
- **Coil Voltage:** 3800 Vac 50 Hz, 440 Vac 60 Hz
- **Contact Configuration:** 1NO
- **Continuous Ampere Rating:** 1000A
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 7.5, 10, 15, 20 hp (3PH
@200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF_C 2D PDF](#)
- [XTCF_C 2D Drawing Xchange](#)
- [XTCF_C AutoCAD 2D Footprint \(mm\)](#)
- [XTCF_C 3D Inventor](#)
- [XTCF_C 3D Model Xchange](#)
- [XTCF_C AutoCAD 2D Footprint](#)



- [Eaton Specification Sheet - XTCF045C10L](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947
- EN 60947

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.