

## Eaton XT IEC contactor

**XTCF063D00B**

### Dimensions:

- **Height:** 4.52755906 IN
- **Length:** 5.78740157 IN
- **Width:** 3.34645669 IN

**Weight:** .48501698 LB

**Notes:** Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

**Warranties:** No Data

### Specifications:

- **Amperage Rating:** 63A
- **Coil Voltage:** 220 Vac 50 Hz, 240 Vac 60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 10, 15, 30, 40 hp (3PH  
@200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF\\_D 3D Inventor](#)
- [XTCF\\_D 2D Drawing Xchange](#)
- [XTCF\\_D AutoCAD 2D Footprint \(mm\)](#)
- [XTCF\\_D AutoCAD 2D Footprint](#)
- [XTCF\\_D 3D Model Xchange](#)
- [XTCF\\_D 2D PDF](#)
- [Eaton Specification Sheet - XTCF063D00B](#)
- [Global Data Sheet - XTCF063D00B](#)

### Certifications:

- UL Listed
- CSA Certified



- IEC 60947
- EN 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.