

Eaton XT IEC contactor

XTCF063D00R

UPC:786685216775

Dimensions:

- **Height:** 3.54 IN
- **Length:** 4.76 IN
- **Width:** 5.75 IN

Weight:2.29 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 63A
- **Coil:** 12V 50/60 Hz
- **Coil Voltage:** 12 Vac, 50-60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 55 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 10, 15, 30, 40 hp (3PH
@200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCF_D AutoCAD 2D Footprint](#)
- [XTCF_D 2D PDF](#)
- [XTCF_D 2D Drawing Xchange](#)
- [XTCF_D 3D Model Xchange](#)
- [XTCF_D AutoCAD 2D Footprint \(mm\)](#)
- [XTCF_D 3D Inventor](#)
- [Eaton Specification Sheet - XTCF063D00R](#)



Certifications:

- EN 60947
- UL Listed
- CSA Certified
- IEC 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.