

## Eaton XT IEC contactor

**XTCF080D00WD**

**UPC:**786685216959

### Dimensions:

- **Height:** 3.54 IN
- **Length:** 4.76 IN
- **Width:** 5.75 IN

**Weight:**2.29 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 80A
- **Coil:** 48 Vdc
- **Coil Voltage:** 48-60 Vdc
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 55 mm
- **Max Hp Rating:** 15, 20, 40, 50 hp (3PH  
@200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCF\\_D 2D Drawing Xchange](#)
- [XTCF\\_D 3D Inventor](#)
- [XTCF\\_D AutoCAD 2D Footprint \(mm\)](#)
- [XTCF\\_D 2D PDF](#)
- [XTCF\\_D 3D Model Xchange](#)
- [XTCF\\_D AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCF080D00WD](#)



**Certifications:**

- UL Listed
- IEC 60947
- EN 60947
- CSA Certified

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.