

Eaton XT IEC contactor

XTCF125G00B

Dimensions:

- **Height:** 6.69291339 IN
- **Length:** 6.88976378 IN
- **Width:** 5.23622047 IN

Weight: .48501698 LB

Notes: Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties: No Data

Specifications:

- **Amperage Rating:** 125A
- **Coil Voltage:** 190V 50 Hz, 240 60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 25, 30, 60, 75 hp (3PH
@200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF_G 2D PDF](#)
- [XTCF_G AutoCAD 2D Footprint](#)
- [XTCF_G AutoCAD 2D Footprint \(mm\)](#)
- [XTCF_G 3D Model Xchange](#)
- [XTCF_G 3D Inventor](#)
- [XTCF_G 2D Drawing Xchange](#)
- [Eaton Specification Sheet - XTCF125G00B](#)
- [Global Data Sheet - XTCF125G00B](#)

Certifications:

- UL Listed



- CSA Certified
- IEC 60947
- EN 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.