

## Eaton XT IEC contactor

**XTCF160G00C**

**UPC:**786685216492

### Dimensions:

- **Height:** 6.7 IN
- **Length:** 5.03 IN
- **Width:** 6.42 IN

**Weight:**6.17 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 160A
- **Coil:** 412V 50 Hz, 480V 60 Hz
- **Coil Voltage:** 480V 50 Hz, 500V 60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 25, 40, 75, 100 hp (3PH @200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCF\\_G 2D PDF](#)
- [XTCF\\_G AutoCAD 2D Footprint \(mm\)](#)
- [XTCF\\_G 2D Drawing Xchange](#)
- [XTCF\\_G 3D Model Xchange](#)
- [XTCF\\_G AutoCAD 2D Footprint](#)
- [XTCF\\_G 3D Inventor](#)
- [Eaton Specification Sheet - XTCF160G00C](#)



**Certifications:**

- CSA Certified
- EN 60947
- UL Listed
- IEC 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.