

## Eaton XT IEC contactor

**XTCF200G00AD**

**UPC:**786685217369

### Dimensions:

- **Height:** 6.7 IN
- **Length:** 5.03 IN
- **Width:** 6.42 IN

**Weight:**6.17 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 200A
- **Coil:** 120 Vdc
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Max Hp Rating:** 40, 50, 100, 125 hp (3PH @200,230,460,575 V)
- **Number Of Poles:** Four-pole
- **Operation:** Non-reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage non-reversing contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCF\\_G 2D PDF](#)
- [XTCF\\_G AutoCAD 2D Footprint \(mm\)](#)
- [XTCF\\_G 2D Drawing Xchange](#)
- [XTCF\\_G 3D Model Xchange](#)
- [XTCF\\_G AutoCAD 2D Footprint](#)
- [XTCF\\_G 3D Inventor](#)
- [Eaton Specification Sheet - XTCF200G00AD](#)

### Certifications:



- UL Listed
- EN 60947
- CSA Certified
- IEC 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.