

# Eaton XT IEC contactor

**XTCR007B21E**

**UPC:**782116884599

## Dimensions:

- **Height:** 28 IN
- **Length:** 21 IN
- **Width:** 22 IN

**Weight:**71 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

## Warranties:

- 1 year

## Specifications:

- **Amperage Rating:** 7A
- **Coil Voltage:** 208 Vac, 60 Hz
- **Contact Configuration:** 2NO-2NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 60 Hz
- **Max Hp Rating:** 0.25, 1/ 1.25, 2, 3, 5 hp (1/3PH  
@ 115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

## Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCR\\_B 3D Inventor](#)
- [XTCR\\_B AutoCAD 2D Footprint \(mm\)](#)
- [XTCR\\_B AutoCAD 2D Footprint](#)
- [XTCR\\_B 3D Model Xchange](#)
- [XTCR\\_B 2D Drawing Xchange](#)
- [XTCR\\_B 2D PDF](#)
- [Eaton Specification Sheet - XTCR007B21E](#)



**Certifications:**

- UL Listed
- EN 60947
- CSA Certified
- IEC 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.