

Eaton XT IEC contactor

XTCR007B21L

UPC:782116884636

Dimensions:

- **Height:** 5 IN
- **Length:** 5.25 IN
- **Width:** 5.75 IN

Weight:1.5 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 7A
- **Coil:** 380V 50 Hz, 440V 60 Hz
- **Coil Voltage:** 3800 Vac 50 Hz, 440 Vac 60 Hz
- **Contact Configuration:** 2NO-2NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 0.25, 1/ 1.25, 2, 3, 5 hp (1/3PH @115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCR_B AutoCAD 2D Footprint](#)
- [XTCR_B 3D Inventor](#)
- [XTCR_B 2D Drawing Xchange](#)
- [XTCR_B 3D Model Xchange](#)
- [XTCR_B AutoCAD 2D Footprint \(mm\)](#)
- [XTCR_B 2D PDF](#)
- [Eaton Specification Sheet - XTCR007B21L](#)



Certifications:

- EN 60947
- IEC 60947
- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.