Eaton XT IEC contactor

XTCR009B21P

UPC:782116884858

Dimensions:

- **Height:** 4 IN
- **Length:** 3.5 IN
- **Width:** 5.5 IN

Weight:1.2 LB

Notes: Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 9A
- **Coil Voltage:** 380 Vac, 50 Hz
- **Contact Configuration:** 2NO-2NO
- **Frame Size:** 45 mm
- **Frequency Rating:** 60 Hz
- **Max Hp Rating:** 0.5, 1.5/ 3, 3, 5, 7.5 hp (1/3PH @115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

Supporting documents:

- Eatons Volume 5-Motor Control and Protection
- XTCR_B 2D Drawing Xchange
- XTCR_B AutoCAD 2D Footprint
- XTCR_B 2D PDF
- XTCR_B 3D Inventor
- XTCR_B AutoCAD 2D Footprint (mm)
- XTCR_B 3D Model Xchange
- Eaton Specification Sheet - XTCR009B21P

Certifications:

- UL Listed
- CSA Certified
- EN 60947
- IEC 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.