

Eaton XT IEC contactor

XTCR025C23T

UPC:786685555171

Dimensions:

- **Height:** 4.5 IN
- **Length:** 4.75 IN
- **Width:** 7.5 IN

Weight:2.45 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:


- **Amperage Rating:** 25A
- **Coil:** 24V 50/60 Hz
- **Coil Voltage:** 24 Vac, 50-60 Hz
- **Contact Configuration:** 1NO integral; 2NO-2NC
- **Frame Size:** 45 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

Supporting documents:

- [Eaton Specification Sheet - XTCR025C23T](#)

Certifications:

- CSA Certified
- EN 60947
- UL Listed
- IEC 60947



Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.