

## Eaton XT IEC contactor

**XTCR040D11BD**

**UPC:**782116885763

### Dimensions:

- **Height:** 6 IN
- **Length:** 6.5 IN
- **Width:** 9.5 IN

**Weight:**4.7 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 40A
- **Coil:** 220 Vdc
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Max Hp Rating:** 3, 7.5/ 10, 15, 30, 40 hp  
(1/3PH @ 115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCR\\_D 2D PDF](#)
- [XTCR\\_D 2D Drawing Xchange](#)
- [XTCR\\_D AutoCAD 2D Footprint \(mm\)](#)
- [XTCR\\_D 3D Inventor](#)
- [XTCR\\_D 3D Model Xchange](#)
- [XTCR\\_D AutoCAD 2D Footprint](#)
- [Eaton Specification Sheet - XTCR040D11BD](#)

### Certifications:



- CSA Certified
- EN 60947
- UL Listed
- IEC 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.