

## Eaton XT IEC contactor

**XTCR050D11E**

**UPC:**782116885992

### Dimensions:

- **Height:** 6 IN
- **Length:** 6.5 IN
- **Width:** 9.5 IN

**Weight:**4.7 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 50A
- **Coil:** 208V 60 Hz
- **Coil Voltage:** 208 Vac, 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Frequency Rating:** 60 Hz
- **Max Hp Rating:** 3, 10/ 15, 20, 40, 50 hp (1/3PH  
@115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCR\\_D AutoCAD 2D Footprint \(mm\)](#)
- [XTCR\\_D 2D Drawing Xchange](#)
- [XTCR\\_D AutoCAD 2D Footprint](#)
- [XTCR\\_D 2D PDF](#)
- [XTCR\\_D 3D Model Xchange](#)
- [XTCR\\_D 3D Inventor](#)
- [Eaton Specification Sheet - XTCR050D11E](#)



**Certifications:**

- CSA Certified
- UL Listed
- EN 60947
- IEC 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.