

Eaton XT IEC contactor

XTCR065D11G

UPC:782116886210

Dimensions:

- **Height:** 6 IN
- **Length:** 6.5 IN
- **Width:** 9.5 IN

Weight:4.7 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 65A
- **Coil:** 190V 50 Hz, 220V 60 Hz
- **Coil Voltage:** 190 Vac 50 Hz, 220 Vac 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 5, 15/ 20, 25, 50, 60 hp (1/3PH
@115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCR_D 2D PDF](#)
- [XTCR_D 2D Drawing Xchange](#)
- [XTCR_D AutoCAD 2D Footprint](#)
- [XTCR_D 3D Model Xchange](#)
- [XTCR_D 3D Inventor](#)
- [XTCR_D AutoCAD 2D Footprint \(mm\)](#)
- [Eaton Specification Sheet - XTCR065D11G](#)



Certifications:

- UL Listed
- EN 60947
- IEC 60947
- CSA Certified

Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.