

# Eaton XT IEC contactor

**XTCR080F00A**

**UPC:**786685104928

## Dimensions:

- **Height:** 6.142 IN
- **Length:** 5.079 IN
- **Width:** 6.535 IN

**Weight:**9.8 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

## Warranties:

- 1 year

## Specifications:

- **Amperage Rating:** 80A
- **Coil:** 110V 50 Hz, 120V 60 Hz
- **Coil Voltage:** 110 Vac 50 Hz, 120 Vac, 60 Hz
- **Contact Configuration:** 0NO-0NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 7.5, 15/ 25, 30, 60, 75 hp  
(1/3PH @115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

## Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTCR080F00A](#)

## Certifications:

- UL Listed
- CSA Certified
- EN 60947
- IEC 60947



**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.