

Eaton XT IEC contactor

XTCR080F11Y

UPC:786685196770

Dimensions:

- **Height:** 6.142 IN
- **Length:** 5.079 IN
- **Width:** 6.535 IN

Weight:9.8 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 80A
- **Coil:** 48V 50 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50 Hz
- **Max Hp Rating:** 7.5, 15/ 25, 30, 60, 75 hp
(1/3PH @ 115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [XTCR_F 3D Model Xchange](#)
- [XTCR_F 2D Drawing Xchange](#)
- [XTCR_F 2D PDF](#)
- [XTCR_F AutoCAD 2D Footprint](#)
- [XTCR_F AutoCAD 2D Footprint \(mm\)](#)
- [XTCR_F 3D Inventor](#)
- [Eaton Specification Sheet - XTCR080F11Y](#)



Certifications:

- UL Listed
- IEC 60947
- CSA Certified
- EN 60947

Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.