

## Eaton XT IEC contactor

**XTCR095F11D**

**UPC:**786685196817

### Dimensions:

- **Height:** 6.142 IN
- **Length:** 5.079 IN
- **Width:** 6.535 IN

**Weight:**9.8 LB

**Notes:**Screw terminals (6-65A); 5 mm (80-150A);  
no lugs (185-2000A)

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 95A
- **Coil:** 550V 50 Hz, 600V 60 Hz
- **Coil Voltage:** 550 Vac 50 Hz, 600 Vac, 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 7.5, 15/ 25, 40, 75, 100 hp  
(1/3PH @115,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [XTCR\\_F 2D Drawing Xchange](#)
- [XTCR\\_F 2D PDF](#)
- [XTCR\\_F AutoCAD 2D Footprint \(mm\)](#)
- [XTCR\\_F 3D Inventor](#)
- [XTCR\\_F AutoCAD 2D Footprint](#)
- [XTCR\\_F 3D Model Xchange](#)
- [Eaton Specification Sheet - XTCR095F11D](#)



**Certifications:**

- EN 60947
- UL Listed
- CSA Certified
- IEC 60947

**Product compliance:**

- CE Marked
- RoHS Compliant

---

© 2016 Eaton. All rights reserved.