

Eaton XT IEC contactor

XTCR170G11L

UPC:786685212876

Dimensions:

- **Height:** 8.25 IN
- **Length:** 10.5 IN
- **Width:** 18.5 IN

Weight:17.2 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 170A
- **Coil:** 380V 50 Hz, 440V 60 Hz
- **Coil Voltage:** 3800 Vac 50 Hz, 440 Vac 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 90 mm
- **Frequency Rating:** 50-60 Hz
- **Max Hp Rating:** 10, 25, 30/ 40, 60, 125, 125 hp
(1/3PH @115,200,230/200,230,460,575 V)
- **Number Of Poles:** Three-pole
- **Operation:** Reversing
- **Series:** XT IEC series
- **Terminals:** Screw terminals
- **Type:** Full voltage reversing contactor

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTCR170G11L](#)

Certifications:

- UL Listed
- EN 60947
- CSA Certified
- IEC 60947



Product compliance:

- RoHS Compliant
- CE Marked

© 2016 Eaton. All rights reserved.