

Specifications



Photo is representative



Eaton CHF120ST

Eaton Type CHF 3/4-inch Standard Circuit Breaker, Single-Pole, 20A, 120/240V, 10 kAIC, (1) #14-8, (2) #14-10 AWG Cu/Al 60°C or 75°C, Shunt Trip

General specifications

PRODUCT NAME	Eaton CH thermal magnetic circuit breaker
CATALOG NUMBER	CHF120ST
UPC	786685384818
PRODUCT LENGTH/DEPTH	4.8 in
PRODUCT HEIGHT	3.5 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.55 lb
WARRANTY	Limited lifetime residential, 1 year commercial
CERTIFICATIONS	UL 489
CATALOG NOTES	Switching Duty Rated, HACR Rated, Single-Pole Requires One 2/4-Inch Space, With Trip Indication.



Powering Business Worldwide

Product specifications

USED WITH	Type CH Loadcenters
TYPE	Type CHF 3/4-inch Standard Circuit Breaker
SPECIAL FEATURES	Shunt Trip
AMPERAGE RATING	20 A
VOLTAGE RATING	120/240 V
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	CH
WIRE SIZE	(1) #14-8 AWG (2) #14-10 AWG Cu/Al
NUMBER OF POLES	Single-pole

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHF120ST
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

