

Specifications

Eaton NQB-A103



Photo is representative

Eaton Navy and Marine complete molded case circuit breaker, NQB-A103, Complete breaker, Non-interchangeable thermal-magnetic trip type, Non-automatic trip rating, Three-pole, 100A, 500 V, Naval, 60/400 Hz

General specifications

PRODUCT NAME	Eaton Navy & Marine complete molded case circuit breaker
CATALOG NUMBER	NQB-A103
UPC	782114653975
PRODUCT LENGTH/DEPTH	8.6 in
PRODUCT HEIGHT	5.8 in
PRODUCT WIDTH	5.8 in
PRODUCT WEIGHT	5.75 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	MIL-DTL-17361
CATALOG NOTES	NSN 5925-01-456-0004



Powering Business Worldwide

Product specifications

AMPERAGE RATING	100 A
VOLTAGE RATING	500 Vac
TRIP TYPE	Non-interchangeable thermal-magnetic
CIRCUIT BREAKER TYPE	NQB-A103
CIRCUIT BREAKER FRAME TYPE	Complete breaker
MAGNETIC TRIP RANGE	Non-automatic
FREQUENCY RATING	60 to 400 Hz
CLASS	Naval
NUMBER OF POLES	Three-pole
TRIP RATING	Non-automatic

Resources

CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - NQB-A103

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.