

## Eaton definite purpose starter

**A27CGC15T004**

**UPC:**782116910571

### Dimensions:

- **Height:** 7.38 IN
- **Length:** 5.81 IN
- **Width:** 5.63 IN

**Weight:**3.11 LB



### Specifications:

- **Model:** Starter
- **Amperage Rating:** 15A
- **Coil:** Coil: 24 V, 50/60 Hz
- **Control Characteristics:** Common control wiring
- **Enclosure:** NEMA Type 1 Enclosed
- **Inductive Full Load:** 15 A IFL
- **Overload Range:** 2.4-4A
- **Phase:** Three-phase
- **Terminals:** Screw/pressure plate
- **Type:** Non-reversing
- **Overload Relay:** 2.4-4 FLA

### Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - A27CGC15T004](#)

### Certifications:

- UL Recognized
- CSA Certified

**Product compliance:** No Data